




Rectangular flat mop Microblue with strap tape system

Highly absorbent microfibre mop with strap tape system support, 25 cm



Technical information

code	notes	cm	C	pcs	kg	m ³
00000712		↕ 25 ↕ 10		25	1,04	0,011

SYSTEM

Flat system with frame with strap tape system, to be used pre-soaked or soaked on demand
Ideal for recurring washing of smooth surfaces

GREEN BOX



EU Ecolabel Certificate



DECITEX of the fibres
Microfibre: 0,16 DTX



Efficient: microfibre requires less chemical to remove dirt and bacteria, reducing water and chemical consumption

Analysis

Analysis of the mechanical action of the Microblue flat mop alone revealed a 99.99% removal of bacteria and fungi present on the surface (test conducted by a specialised external laboratory adapting the UNI EN 16615:2015 standard).
The analysis of the mechanical action of the Microblue mop revealed a removal of Coronavirus 229E from steel surfaces of 99.9% (test conducted by a specialised external laboratory)

Advantages

- **Highest hygiene:** Microfibre penetrates the micro-pores in the floor, collecting dirt and 99.99% of bacteria

Material

Yarn: microfibre (85% polyester, 15% polyamide) - Support: polyester

Packaging: [click here to see the environmental labelling of packaging](#)

Washing conditions

Guidelines for proper fibre maintenance

Follow the washing instructions (temperatures and dosage) on the laundry detergent packaging
 Perform a pre-wash in cold water without laundry detergent to remove any residual product used during cleaning operations
 Recommended use of professional textile laundry detergent
 Do not use fabric softener
 Do not use laundry detergents with Ph > 11
 The use of laundry nets is recommended to speed up and make laundry operations more hygienic

Specific mop instructions



Washing temperature max 90° C, recommended 60°




Bleaching possible, do not use chlorine



Tumble dry or in a dryer possible with low program

Related products



Velook Lampo rectangular frame



Mini telescopic handle



Telescopic handle